




## DFNL

### Asphere metrology using Diffractive Fizeau Null Lenses



- Easy handling: Measuring aspheres as easy as measuring spheres
- Compatible with standard interferometer bayonet mount
- With integrated Fizeau reference plane
- Measurement of the vertex radius of curvature with integrated cat-eye beam
- Plane surface for recalibration of the Fizeau plane

<b>Size of bayonet mount</b>	2" to 12"
<b>Maximum active area</b>	diameter < 220 mm
<b>Integrated alignment features</b>	Optional: Cat-eye beams
<b>Lowest f-number</b>	f/0.9
<b>Measuring accuracy</b>	< PV $\lambda/20$ ( $\lambda/40$ with calibration)



Distribution in the UK & Ireland



**Lambda Photometrics Limited**  
 Lambda House Batford Mill  
 Harpenden Herts AL5 5BZ  
 United Kingdom  
**E:** [info@lambdaphoto.co.uk](mailto:info@lambdaphoto.co.uk)  
**W:** [www.lambdaphoto.co.uk](http://www.lambdaphoto.co.uk)  
**T:** +44 (0)1582 764334  
**F:** +44 (0)1582 712084