



## Acuros<sup>®</sup> CQD<sup>®</sup> 1280 USB3 SWIR Camera

Acuros<sup>®</sup> CQD<sup>®</sup> cameras are the highest pixel resolution SWIR cameras sold commercially, enabling users to see features with the finest details. Our novel CQD sensors deliver full visible-to-SWIR band response, achieving lower costs per megapixel compared to InGaAs SWIR cameras. The Acuros CQD 1280 SWIR camera is designed with an integrated, multi-purpose 1280x1024 TEC Cooled CQD sensor, resulting in low noise and highly stable performance. Acuros cameras have up to a 10db higher SNR than competitive 5 $\mu$ m pixel InGaAs cameras.

### Specifications:

#### Electro-Optical Specifications:

Sensor	Acuros <sup>®</sup> CQD <sup>®</sup> sensor
Temperature stabilization	Single-stage thermo-electric cooler
Sensor array format	1280 x 1024
Resolution	1.31 megapixels
Spectral band	400 nm - 1700 nm
Array size	19.2mm x 15.4 mm, 24.6 mm diagonal
Pixel pitch	15 $\mu$ m x 15 $\mu$ m
Max frame rate at full resolution	88 fps (8, 10, 12, 14 bit)
Pixel operability	99.9% typical, 99.75% min
Bit depth	8, 10, 12, 14 bit selectable
Integration type	Snapshot global shutter
Trigger	External TTL
Integration time	10 $\mu$ sec to 4 sec
Dynamic range	70 dB typical
Windowing & windowing frame rate	Array centered. Scales inversely to window size
Laser beam fringeless operation	No (See Acuros Laser Series Cameras)
Binning arrays	2 x 2, 4 x 4
Non-uniformity correction	2-point non-uniformity correction
Temporal dark noise	65e <sup>-</sup> typical (high gain)
Quantum efficiency	See typical QE curve.

### Features:

- HD resolution
- TEC cooling
- Low noise
- Fast frame rate
- Visible-SWIR
- USB3 Vision
- High value

### Applications:

- Machine vision
- Silicon inspection
- Automotive
- Fill-level
- Surveillance
- Hyperspectral
- Chemical sensors
- Agricultural
- Medical imaging
- Thermography



# SWIR<sup>®</sup>

VISION SYSTEMS

High Definition. SWIR Vision.

## Specifications:

### Environmental & power specifications, typical performance

Operating case temperature	-20 °C to +55 °C
Power consumption	6.5 - 12 W depending on TEC settings
Power supply voltage	6-16 VDC
Regulatory compliance	CE mark

### Mechanical specifications

Dimensions excluding lens	6.1 x 6.1 x 9.7 cm (C-Mount)
Weight excluding lens	508 grams with C-mount adaptor, 594g (F-mount)
Lens mounts	C-, F-Mount, M42 (C-Mount flange-back distance)
Power connector	Hirose 12-pin, HR10A-10R-12PB (71)
Trigger connector	BNC

### Software and user interface

Software development kit	Windows GUI and Pleora eBUS SDK ( <i>Linux, Windows, MacOS</i> )
GenICam compliance	Yes
Interface	USB3 Vision

### Export compliance

US export designation	EAR-99. No license required for lawful export
-----------------------	---

### Ordering

Part numbers	1280: Acuros-1280-USB3-001
--------------	----------------------------




C-mount, F-mount, and M-42 Lens Mounts




USB3 Vision Interface

## Acuros CQD SWIR camera images



## Typical QE Performance



- a. Acuros 640: imaging through maritime rain event
- b. Acuros 640: imaging through pharmaceutical vial labels
- c. Acuros 1280: alignment mark in bonded wafers
- d. Acuros 1920: mag image of semiconductor chip edge

Acuros-1280-USB3-001





# SWIR<sup>®</sup>

VISION SYSTEMS

High Definition. SWIR Vision.

## Mechanical Drawings C Mount



GEN*i*CAM

GIG  
VISION

CE

Acuros-1280-USB3-001





# SWIR<sup>®</sup>

VISION SYSTEMS

High Definition. SWIR Vision.

## Mechanical Drawings M42 Short Mount



Distribution in the UK & Ireland



**Lambda Photometrics Limited**  
Lambda House Batford Mill  
Harpenden Herts AL5 5BZ  
United Kingdom

**Characterisation,  
Measurement &  
Analysis**

**E: [info@lambdaphoto.co.uk](mailto:info@lambdaphoto.co.uk)**  
**W: [www.lambdaphoto.co.uk](http://www.lambdaphoto.co.uk)**  
**T: +44 (0)1582 764334**  
**F: +44 (0)1582 712084**



GEN*i*CAM

**GiGE**  
VISION



Acuros-1280-USB3-001