


**U3PE-FL1009**  
PCI express x1 Gen2 adapter,  
2x USB 3.0 ports, Fresco  
Logic FL1009

**U3PE-D720202**  
PCI express x1 Gen2 adapter,  
2x USB 3.0 ports, Renesas  
D720202



**CBL-MQSYNC-3M0**  
3.0m MQ series sync pigtail cable, thread lock, 3 poles:  
ground, Trigger In, Strobe Out



**CBL-U3-3M0**  
3.0m USB 3.0 cable with thumbscrews on Micro B connector

**CBL-U3-5M0**  
5.0m USB 3.0 cable with thumbscrews on Micro B connector


**CBL-U3-8M0**  
5.0m USB 3.0 cable with thumbscrews on Micro B connector

**CBL-U3-xMOX**  
Same as three above with thumbscrews on both connectors

**CBL-U3A-10M0**  
10.0m USB 3.0 cable, active cable repeater

**CBL-U3A-15M0**  
15.0m USB 3.0 cable, active cable repeater


**CBL-U3A-20M0**  
20.0m USB 3.0 cable, active cable repeater



### xiQ C-mount configuration:

| MODEL      | RES.      | FPS    | B/C   | DIMENSION[mm]* |
|------------|-----------|--------|-------|----------------|
| MQ003MG-CM | 648x488   | 300fps | B/W   | 25.4x25.4x24.6 |
| MQ003CG-CM | 648x488   | 300fps | Color | 25.4x25.4x24.6 |
| MQ013MG-E2 | 1240x1024 | 60fps  | B/W   | 25.4x25.4x26.7 |
| MQ013CG-E2 | 1240x1024 | 60fps  | Color | 25.4x25.4x26.7 |
| MQ013MG-ON | 1240x1024 | 150fps | B/W   | 25.4x25.4x26.7 |
| MQ013CG-ON | 1240x1024 | 150fps | Color | 25.4x25.4x26.7 |
| MQ022MG-CM | 2048x1088 | 180fps | B/W   | 25.4x25.4x30.7 |
| MQ022CG-CM | 2048x1088 | 180fps | Color | 25.4x25.4x30.7 |
| MQ042MG-CM | 2048x2048 | 90fps  | B/W   | 25.4x25.4x30.7 |
| MQ042CG-CM | 2048x2048 | 90fps  | Color | 25.4x25.4x30.7 |

\* WxHxL. Dimensions are for the C-mount configuration  
CS mount configuration is 5mm shorter



### MQ-BRACKET-T

xiQ series tripod mounting bracket with 1/4-20 thread  
Use 4x SROB-M2x4-CUST screws for mounting  
Bracket can be mounted on the bottom or top side of the camera.

Distribution in the UK & Ireland



**Lambda Photometrics Limited**  
Lambda House Batford Mill  
Harpenden Herts AL5 5BZ  
United Kingdom

**E:** [info@lambdaphoto.co.uk](mailto:info@lambdaphoto.co.uk)  
**W:** [www.lambdaphoto.co.uk](http://www.lambdaphoto.co.uk)  
**T:** +44 (0)1582 764334  
**F:** +44 (0)1582 712084

### xiQ CS-mount configuration:

| MODEL         | RES.      | FPS    | B/C   | DIMENSION[mm]* |
|---------------|-----------|--------|-------|----------------|
| MQ003MG-CM-CS | 648x488   | 300fps | B/W   | 25.4x25.4x19.6 |
| MQ003CG-CM-CS | 648x488   | 300fps | Color | 25.4x25.4x19.6 |
| MQ013MG-E2-CS | 1240x1024 | 60fps  | B/W   | 25.4x25.4x21.7 |
| MQ013CG-E2-CS | 1240x1024 | 60fps  | Color | 25.4x25.4x21.7 |
| MQ013MG-ON-CS | 1240x1024 | 150fps | B/W   | 25.4x25.4x21.7 |
| MQ013CG-ON-CS | 1240x1024 | 150fps | Color | 25.4x25.4x21.7 |
| MQ022MG-CM-CS | 2048x1088 | 180fps | B/W   | 25.4x25.4x25.7 |
| MQ022CG-CM-CS | 2048x1088 | 180fps | Color | 25.4x25.4x25.7 |
| MQ042MG-CM-CS | 2048x2048 | 90fps  | B/W   | 25.4x25.4x25.7 |
| MQ042CG-CM-CS | 2048x2048 | 90fps  | Color | 25.4x25.4x25.7 |

\* WxHxL. Dimensions are for the Cs-mount configuration  
C mount configuration is 5mm longer

